

INDOOR FILTERFANS 500–710 m³/h



size



protection system



tool-less filter mat
changing



tool-less mounting



PRODUCT	PFB 65.000SL	PFB 66.000SL	PFB 67.000SL	
ARTICLE NO.	11675102955	11676102955	11677102955	Unit

Rated voltage ±10 %	AC 50 60 Hz			
	230			V
Unimpeded airflow	500 560	600 614	700 710	m ³ /h
Airflow rate in combination with exhaust filter	360 390	385 390	445 475	
Power consumption	67 82	116 151	130 170	W
Current consumption	0.31 0.35	0.51 0.65	0.58 0.78	A
Type of connection	terminal strip			
Temperature range	-10 ... +55 -14 ... +131			°C °F
Service life L ₁₀ (+ 40 °C)	35000			h
Dimensions (X x Y)	320 x 320			mm
Installation depth (Z2) + Construction height (Z1)	127 + 7	131 + 7		
Cut-out dimensions (W x H)	291 x 291			

ACCESSORIES		ARTICLE NUMBER
Exhaust filter	grey	11760002955
Spare filter mats	5 pieces	18611600161
Thermostat		17121000000
Hygostat		17207000000
Rainhood in stainless steel		18182000020

For additional models, options and voltages visit www.pfannenberg.com or contact us directly.



¹ for material thicknesses up to 2 mm
+ 1 mm for thickness of material > 2 mm ≤ 3 mm

Comprehensive technical documentation such as

- operating instruction, technical data, approvals
- cut-out drawing, CAD | EPLAN | Zuken | WSCAD data

can be retrieved by entering this webcode in the search window on www.pfannenberg.com

